



Wattstopper
Dual Relay Resi VAC Sensor w Nightlight 600W White, Box
Part No. CS-350-N-W



The CS-350-N Passive Infrared (PIR) Dual Relay Vacancy Sensor provides automatic lighting shutoff for applications that require separate switching of two loads. It is engineered to comply with specific provisions of California's Title 24-2013 energy code.

Features & Benefits

Collection consolidated to white option

Manual-on/automatic-off control of two separate loads

Integral LED nightlight

Ideal for bathrooms

Adjustable time delay

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Gloss	UPC Number	754182923380
Country Of Origin	China	Material	ABS
Product Series	CS-350-N	Features	Adjustable Time Delay, Dual Relay, Indicator Lights, Locator Light
Switch Type	Push	Installation Location	Wall
Included	Mounting Screws, Wire Nuts	Application Sector	Commercial, Residential
Standard	UL, cUL, Complies with 2011 NEC requirements, California Title 24 Compliant	Warranty Type	5-Year
Type	Sensor, Switch		

Dimensions

Product Width US	1.8 in	Product Weight US	0.2502 lb
Product Volume US	40.62 cu in	Product Depth US	1.8 in
Product Height US	4.1 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	Trimpot
Load Rating	600 W @ 120 VAC	Has Battery	No
Sensor Coverage Pattern	180 °	Sensor Type	Vacancy
Operating Temperature Max	131 °F	Number of Gangs	1
Sensor Mounting Height	4 ft	Number of Buttons	2
Number of Rockers	0	Sensor Technology	Passive Infrared (PIR)
Timer Duration	15 Seconds, 15 Minutes, 30 Minutes	Number of Poles	Single Pole
Indicator	PIR Detection LED	Input Voltage	120 V
Requires Neutral Wire	Yes	Line Frequency	60 Hz
Indoor/Outdoor	Indoor	Sensor Coverage	600 sq ft
Mounting Type	In-Wall	On Function	Manual On
Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Sensing Range	24 x 25 ft	Location Rating	Dry
Wire Connection Type	Flying Leads	Engraving Type	Blank
Storage Temperature	23° - 176° F, -5° - 80° C		