



Pass and Seymour
20A 125V Hospital-Grade Tamper-Resistant Duplex Receptacle, Back and Side Wire, Red
Part No. TR63HRED

Tamper-Resistant Hospital Grade Receptacles, Back and Side Wire, 20A, 125V



Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.	AC receptacles available in 15 and 20 Amp, 125V
Extra heavy-duty brass, one-piece mounting strap with integral ground.	One-piece, nickel-plated: brass, triple-wipe power contacts for lasting retention.
Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.	Impact-resistant nylon face and back body.
Two drive screws anchor strap to back body and face.	Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Finish	Matte	UPC Number	785007145267
Country Of Origin	Mexico	Number of Receptacles	2
Features	Brass Mounting Strap	Outlet Type	Hospital Grade, Tamper-Resistant
Application Sector	Commercial, Healthcare	Wall Plate Included	No

Standard	UL498, CSA C22.2 No. 42, FEDSPEC	Warranty Type	1-Year Limited Warranty
Dimensions			
Product Width US	1.625 in	Product Depth US	0.9 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Operating Temperature	-40°-60°C
Wire Connection Type	Screw Terminals	Voltage	125.0 V