



Wattstopper
Resi PIR Vacancy Sensor, 2-wire, White
Part No. CS-50-W



The CS-50 Passive Infrared (PIR) Vacancy Sensor provides automatic shutoff for single-pole lighting control applications. It is engineered to comply with specific provisions of California's Title 24-2013 energy code.

Features & Benefits

Collection consolidated to white option

Manual-on/automatic-off control

LED status indicator

Adjustable time delay

Two-wire sensor; no neutral connection

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Gloss	UPC Number	754182926923
Country Of Origin	China	Material	ABS
Product Series	CS-50	Features	Adjustable Time Delay, Indicator Lights
Switch Type	Push	Installation Location	Wall
Included	Mounting Screws, Wire Nuts	Application Sector	Commercial, Residential
Standard	UL, cUL, California Title 24 Compliant	Warranty Type	5-Year
Type	Sensor, Switch		

Dimensions

Product Width US	1.8 in	Product Weight US	0.2095 lb
Product Volume US	23.805 cu in	Product Depth US	1.4 in
Product Height US	4.1 in		

Additional Information

RoHS Compliant	Yes	Security	Yes
----------------	-----	----------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	Trimpot
Load Rating	600 W @ 120 VAC	Has Battery	No
Sensor Coverage Pattern	180 °	Sensor Type	Vacancy
Operating Temperature Max	131 °F	Number of Gangs	1
Sensor Mounting Height	4 ft	Number of Buttons	1
Number of Rockers	0	Sensor Technology	Passive Infrared (PIR)
Timer Duration	30 Seconds, 5-30 Minutes	Number of Poles	Single Pole
Indicator	PIR Detection LED	Input Voltage	120 V
Line Frequency	60 Hz	Indoor/Outdoor	Indoor
Sensor Coverage	600 sq ft	Mounting Type	In-Wall
On Function	Manual On	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	24 x 25 ft
Location Rating	Dry	Wire Connection Type	Flying Leads
Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C