



Pass and Seymour
20A Heavy Duty Power Indicating Hospital-Grade Receptacle, Red
Part No. TR8300HPIRED



Built for the harshest medical environments, Pass and Seymour power indicating receptacles feature two industry-exclusive green LEDs that offer clear visual assurance of power indication at the receptacle even with critical equipment plugged into the device. The LEDs operate independently from one another to accommodate split-circuit wiring installations. Tamper-resistant protection comes standard with each receptacle to further enhance safety.

Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.

Extra heavy-duty galvanized steel, one-piece mounting strap with integral ground.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Exclusive patented feature, circuit label on face allows permanent circuit identification.

One-piece, nickel-plated: brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and back body.

Two drive screws anchor strap to back body and face.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

For covering patents, see www.legrand.us/patents.

Wire Size: #14 - #10 AWG Copper Conductor Only

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007041712	Country Of Origin	Mexico
Number of Receptacles	2	Features	Single Piece Plated Steel Mounting Strap

Outlet Type	Hospital Grade, Tamper-Resistant	Application Sector	Commercial, Healthcare
Wall Plate Included	No	Standard	CSA Listed, UL Listed, FSUL, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.625 in	Product Depth US	0.9 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Is Tamper-Resistant	Yes	Connection Location	Back and Side
Phase	Single	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Operating Temperature	-40°-60°C	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	125.0 V	Environmental Conditions	UL94 V2