



Pass and Seymour

20A 125V Hospital-Grade Tamper-Resistant Compact Duplex Receptacle, Back and Side Wire, White

Part No. TR8300HW



Hospital-Grade Tamper-Resistant Compact Design Receptacle, Back and Side Wire, 20A, 125V

Features & Benefits

Impact-resistant nylon face.

Stainless steel mounting screws also resist corrosion.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.

High strength thermoplastic back body.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Meets National Electrical Code Tamper-Resistant requirements.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Wire Size: #14 - #10 AWG Copper Conductor Only

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007035278
Country Of Origin	Mexico	Number of Receptacles	2
Features	Single Piece Plated Steel Mounting Strap	Outlet Type	Hospital Grade, Tamper-Resistant
Application Sector	Commercial, Healthcare	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Wire Connection Type	Screw Terminals	Voltage	125.0 V