



Pass and Seymour
Tamper-Resistant Isolated Ground Hospital Grade Receptacle, Back and Side Wire, 20A, 125V, Orange
Part No. TRIG8300



Tamper-Resistant Isolated Ground Hospital Grade Duplex Receptacle, Back and Side Wire, 20amp 125volt, Orange. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007011951	Country Of Origin	Mexico
Number of Receptacles	2	Features	Single Piece Plated Steel Mounting Strap
Outlet Type	Hospital Grade, Isolated Ground, Tamper-Resistant	Application Sector	Commercial, Healthcare
Wall Plate Included	No	Standard	cULus UL498, FEDSPEC
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.187 in	Product Depth US	1.25 in
Product Height US	2.25 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Connection Location	Back and Side	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Wire Connection Type	Screw Terminals
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2