



radiant Collection
radiant® Tamper-Resistant Outlet, Black
Part No. 885TRBKCC8



Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Features durable, high-impact resistant thermoplastic construction.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisible shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Back and side wire termination options accepts #14-#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Satin	UPC Number	785007277807
Country Of Origin	China	Number of Receptacles	2
Features	Decorator Style	Outlet Type	Straight Blade, Tamper-Resistant
Application Sector	Hospitality, Residential	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
------------------	---------	------------------	--------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Wire Connection Type	Push Wire	Voltage	120.0 V, 125.0 V