



radiant Collection
radiant® Two Single-Pole Switches, Ivory
Part No. RCD11I



Control two separate lights or devices from a single location with this combination switch. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Offers installation flexibility with space-saving style, as part of the extensive offering from the radiant® Collection. Features durable, high-impact resistant thermoplastic construction.

Designed to install easily with a narrower back body and captivated mounting screws. Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.

More color options available to fit any style, including finishes to match current hardware and lighting trends. Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Satin	UPC Number	785007054842
Country Of Origin	China	Material	Thermoplastic
Features	Combination, Decorator Style, Locator Light	Switch Type	Paddle
Number of Switches	2	Application Sector	Residential
Wall Plate Included	No	Standard	cULus, UL Listed
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.29 in	Product Depth US	1.59 in
Product Height US	3.81 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140597	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Load Rating	15 A @ 120/125 VAC	Operating Cycles	50000
Connection Location	Back and Side	Terminal Accommodation	#14 AWG - #12 AWG
Number of Gangs	1	Throw Type	Single Throw
Amperage	15 A	Number of Poles	3-Way, Single Pole
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Location Rating	Dry
Wire Connection Type	Push Wire, Wire Terminal	Voltage	120 VAC, 125 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon	Environmental Conditions	UL94 V2