



Wattstopper
CONTACTOR - 4 POLE NORMALLY OPEN 277V COI
Part No. C277NO



The Multi-pole Contactor is a compact, electrically held lighting contactor used for controlling lighting and other electrical loads in Watt Stopper Lighting Integrator (LI) lighting control panels.

Features & Benefits

Multi-pole design enables control of multiple single-phase or multi-phase loads

Silver cadmium oxide contacts for long life

Normally closed or normally open contacts

Four pole, SPST power contacts

Compatible with all HID and electronic ballast loads

Accepts wire gauge #10-#14 AWG

Specifications

General Info

Product Line	Wattstopper	Color	Black
UPC Number	754182926893	Country Of Origin	China
Material	ABS	Installation Location	Enclosure
Application Sector	Commercial	Standard	UL, CSA
Warranty Type	1-Year	Type	Contactor

Dimensions

Product Width US	1.7 in	Product Weight US	0.7 lb
Product Volume US	14.3 cu in	Product Depth US	2.9 in
Product Height US	2.9 in		

Additional Information

RoHS Compliant	Yes	DesignLights Consortium Qualified System	Yes
Security	Yes		

Technical Information

Operating Temperature Min	32 °F	Load Rating	30 A @ 600 VAC
Compatibility	LMCP Panels	Wire Gauge	10-14 AWG
Number of Connections	4	Contact Configuration	N-O
Contact Rating	277 V	Operating Temperature Max	131 °F
Number of Relays	0	Input Voltage	277 V
Line Frequency	50 Hz, 60 Hz	Indoor/Outdoor	Indoor
Mounting Type	DIN Rail	Operating Temperature	32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Location Rating	Dry
Wire Connection Type	Screw Terminal	Storage Temperature	23° - 176° F