



Wattstopper
DLM Wired Standard Sensor Switch, 1B 1R
Part No. LMDW-211-W-U



LMDW-200 Series Wall Switch and Sensor devices are programmable, low voltage devices which provide both occupancy sensing and manual control of one or more loads from one or more locations. They are part of the Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

Features & Benefits

Software lockable configuration button, accessible without faceplate removal

Digital Lighting Management components plug together on a free-topology Category 5e DLM local network

Infrared (IR) transceiver for wireless configuration and control

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Matte	UPC Number	754182000029
Country Of Origin	United States	Material	ABS
Product Series	LMDW-200	Features	Adjustable Time Delay, Indicator Lights, Load Controller Required, Sensitivity Adjustment
Switch Type	Motion Sensor, Push, Rocker	Number of Switches	2
Installation Location	Wall	Included	Mounting Screws

Application Sector	Commercial	Standard	UL, cUL, FCC part 15, RoHS, PEP, BAA
Warranty Type	5-Year	Type	Sensor, Switch
Dimensions			
Product Width US	1.6 in	Product Weight US	0.1 lb
Product Depth US	1.6 in	Product Height US	4.1 in
Listing Agencies / 3rd Party Agencies			
FCC Compliant	Yes		
Trade Programs			
BAA	Yes		
Additional Information			
RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
Technical Information			
Operating Temperature Min	32 °F	Timer Type	Digital
Compatibility	DLM Wired, Infrared Wireless	Ultrasonic Frequency	40 kHz
Has Battery	No	Sensor Coverage Pattern	180 °
Sensor Type	Occupancy	Operating Temperature Max	131 °F
Sensor Mounting Height	4 ft	Number of Buttons	1
Number of Rockers	1	Sensor Technology	Dual Technology, Passive Infrared (PIR), Ultrasonic

Timer Duration	1-30 Minutes	Topology	Free Topology
Indicator	Button LED, PIR Detection LED, Sensor Binding (PNL) LED, Ultrasonic Detection LED	Input Voltage	24 VDC
Indoor/Outdoor	Indoor	Sensitivity Adjustment	PIR (0-100%), Ultrasonic (0-100%)
Mounting Type	In-Wall	On Function	Selectable Auto/Manual
Current Draw	20 mA	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	30 x 30 ft, 40 ft radius
Location Rating	Dry	Wire Connection Type	RJ-45
Engraving Type	Icon	Storage Temperature	23° - 176° F, -5° - 80° C