



Wattstopper
Low Voltage PIR Ceiling Occupancy Sensor, 500 sq ft, 24VDC
Part No. CI-305-1



Wattstopper's CI-300 Passive Infrared (PIR) Ceiling Sensors automatically turn lighting on and off based on occupancy. The sensor mounts on the ceiling with a flat, low-profile appearance and provides 360 degrees of coverage.

Features & Benefits

- Architecturally appealing low-profile appearance
- Automatic or manual-on operation when used with a BZ-150 Power Pack
- Plug terminal wiring for quick and easy installation
- Accepts low-voltage switch input for manual-on operation
- Walk-through mode increases savings potential
- 360° coverage

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182914326	Country Of Origin	China
Material	ABS	Product Series	CI-305
Features	Adjustable Time Delay, Indicator Lights, Light Level Sensor, Power Pack Required, Sensitivity Adjustment	Installation Location	Ceiling
Included	Spring Clips	Application Sector	Commercial
Standard	UL, cUL	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	4.5 in	Product Weight US	0.2 lb
------------------	--------	-------------------	--------

Product Volume US	44.4 cu in	Product Depth US	1.6 in
Product Height US	4.5 in		
Additional Information			
RoHS Compliant	Yes	Security	Yes
Product Environmental Profile	Yes		
Technical Information			
Operating Temperature Min	32 °F	Has Battery	No
Sensor Coverage Pattern	360 °	Sensor Type	Occupancy
Operating Temperature Max	131 °F	Sensor Mounting Height	8-12 ft
Sensor Technology	Passive Infrared (PIR)	Indicator	LED Light
Input Voltage	24 VDC/VAC	Indoor/Outdoor	Indoor
Sensor Coverage	1200 sq ft	Sensitivity Adjustment	PIR (Min/Max)
Mounting Type	4 in Octagonal J-Box, Ceiling Tile, Surface	On Function	Auto On
Current Draw	9 mA	Operating Temperature	0°-55°C, 32°-131°F
Sensing Range	44 ft diameter	Wire Connection Type	Plug Terminal