



**Wattstopper**  
**Network accessory enclosure 4 routers, 8 port switches**  
Part No. LMNC-4

The LMNC is a surface-mount NEMA1-rated enclosure with DIN rails for mounting DLM network components. Comes with hinged cover and provided empty (LMNC-MT) or with 1–9 installed routers. Based on the catalog number suffix, a specific number of NB-ROUTERS and an NB-SWITCH can be installed in the panel and pre-wired to a power supply. Two single outlets are provided on the power supply, one for connecting an LMJA Network Controller plug-in power supply, and a convenience outlet for a laptop or other technician required components.

## Features & Benefits

NEMA1-rated enclosure

DIN rail mounting for easy installation or removal of the LMJA Network Controller (ordered separately)

Includes selection of pre-wired NB-ROUTERS and NB-SWITCH

Single termination point for one 120VAC circuit to power all devices

Power supply with two 120V outlets for Network Controller power and laptop or other set up tools

## Specifications

### General Info

|                     |                  |                    |                                                                                             |
|---------------------|------------------|--------------------|---------------------------------------------------------------------------------------------|
| Product Line        | Wattstopper      | Color              | Gray                                                                                        |
| Finish              | Gloss, Painted   | UPC Number         | 754182938179                                                                                |
| Country Of Origin   | United States    | Material           | Steel                                                                                       |
| Product Series      | LMNC             | Included           | 4 Routers, 8 Network Ports, Data Cables, DIN Rails, Hinged Door, Power Supply, Power Wiring |
| Number of Knockouts | 1                | Application Sector | Commercial                                                                                  |
| Standard            | UL, ANSI 61, BAA | Warranty Type      | 5-Year                                                                                      |
| Type                | Enclosure        |                    |                                                                                             |

## Dimensions

|                        |                 |                                          |                        |
|------------------------|-----------------|------------------------------------------|------------------------|
| Product Width US       | 16.0 in         | Product Depth US                         | 5.4 in                 |
| Product Height US      | 10.5 in         | Enclosure Size                           | 20 in                  |
| Knockout Size          | 1 in            |                                          |                        |
| Trade Programs         |                 |                                          |                        |
| BAA                    | Yes             |                                          |                        |
| Additional Information |                 |                                          |                        |
| RoHS Compliant         | Yes             | DesignLights Consortium Qualified System | Yes                    |
| Security               | Yes             |                                          |                        |
| Technical Information  |                 |                                          |                        |
| Compatibility          | DLM Wired       | Power Supply                             | 120 - 24VAC            |
| Gauge                  | 14              | Mounting Hole Type                       | Keyhole                |
| Enclosure Type         | NEMA 1, Network | Configuration                            | With Router and Switch |
| Input Voltage          | 120 VAC         | Line Frequency                           | 50 Hz, 60 Hz           |
| Cable Entry            | Knockout        | Mounting Type                            | Screw Mount            |
| Location Rating        | Dry             | Mounting                                 | Wall                   |