



Wattstopper
PIR Ceiling Occupancy Sensor 50 linear sq. ft. 24 VDC
Part No. CX-105-4



Wattstopper's CX-100 Series Passive Infrared (PIR) Ceiling/Wall Sensors detect occupancy to control lighting in a wide variety of applications. These sensors provide superior coverage and performance with great energy savings.

Features & Benefits

Turns lights on and off based on occupancy

User-adjustable time delay and sensitivity

ASIC technology reduces components and provides greater reliability

Choice of four coverage patterns

Built-in light level sensor

Isolated relay for use with HVAC or other control systems

Automatic or manual-on operation when used with a BZ-150 Power Pack

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182911424	Country Of Origin	China
Material	ABS	Product Series	CX-100
Features	Adjustable Time Delay, Indicator Lights, Light Level Sensor, Power Pack Required, Sensitivity Adjustment	Installation Location	Ceiling, Wall
Included	J-Box Cover Plate, Sensor Mask, Swivel Bracket	Application Sector	Commercial
Standard	UL, cUL, ISO 9002	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	3.4 in	Product Weight US	0.3 lb
Product Volume US	75.7 cu in	Product Depth US	3.1 in
Product Height US	4.25 in		

Additional Information

RoHS Compliant	Yes	Security	Yes
----------------	-----	----------	-----

Technical Information

Compatibility	EN-SIM-AI/SPS-GB2-BK	Has Battery	No
Sensor Type	Occupancy	Sensor Mounting Height	30 ft
Sensor Technology	Passive Infrared (PIR)	Indicator	LED Light
Input Voltage	24 VDC/VAC	Line Frequency	60 Hz
Indoor/Outdoor	Indoor	Sensor Coverage	50 ft
Sensitivity Adjustment	PIR (Min/Max)	Mounting Type	Industrial Bracket, J-Box, Surface, Swivel Bracket
On Function	Auto On	Current Draw	8 mA
Sensing Range	6 x 50 ft	Wire Connection Type	Flying Leads