



**Wattstopper**  
**Discontinued - Digital Enhanced Plug Load Controller, On/Off, 120V, 60Hz**  
Part No. LMPL-201



LMPL-201 Plug Load Controllers include a 20 amp relay for on/ off control of connected outlets, and a high-efficiency switching power supply. They are part of a Wattstopper Digital Lighting Management (DLM) system, and enable energy-efficient control of plug loads.

## Features & Benefits

|                                                                                            |                                                                          |
|--------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|
| Plenum-rated controller with line voltage relay and switching power supply                 | Component of Digital Lighting Management integrated control systems      |
| Plugs to other components using Cat 5e cable and RJ45 connectors eliminating wiring errors | Plug n' Go automatic configuration and Push n' Learn for personalization |
| Integral current monitoring of total connected load                                        | Accepts occupancy sensor signal for energy saving control of plug loads  |

## Specifications

### General Info

|                       |                                               |                         |              |
|-----------------------|-----------------------------------------------|-------------------------|--------------|
| Product Line          | Wattstopper                                   | Replaced by Part Number | LMPL-111-20M |
| Color                 | White                                         | Finish                  | Gloss        |
| UPC Number            | 754182928842                                  | Country Of Origin       | China        |
| Material              | ABS                                           | Product Series          | LMPL         |
| Installation Location | Ceiling                                       | Application Sector      | Commercial   |
| Standard              | UL 88T9, UL 2043, cUL, FCC part 15, PEP, RoHS | Warranty Type           | 5-Year       |
| Type                  | Room Controller                               |                         |              |

### Dimensions

|                   |             |                   |        |
|-------------------|-------------|-------------------|--------|
| Product Width US  | 6.5 in      | Product Weight US | 1.5 lb |
| Product Volume US | 231.0 cu in | Product Depth US  | 3.0 in |
| Product Height US | 6.5 in      |                   |        |

Additional Information

|                |     |                                          |     |
|----------------|-----|------------------------------------------|-----|
| RoHS Compliant | Yes | DesignLights Consortium Qualified System | Yes |
| Security       | Yes |                                          |     |

Technical Information

|                           |                    |                           |                           |
|---------------------------|--------------------|---------------------------|---------------------------|
| Operating Temperature Min | 32 °F              | Output Voltage            | 24 VDC                    |
| Load Rating               | 20 A @ 120 VAC     | Compatibility             | DLM Wired                 |
| Has Battery               | No                 | Number of Connections     | 4                         |
| Dimming Compatibility     | On/Off             | Operating Temperature Max | 158 °F                    |
| Topology                  | Free Topology      | Number of Relays          | 1                         |
| Input Voltage             | 120 V              | Line Frequency            | 50 Hz, 60 Hz              |
| Indoor/Outdoor            | Indoor             | Mounting Type             | 4 in Deep J-Box           |
| Operating Temperature     | 0°-70°C, 32°-158°F | Operating Humidity        | 5-95% RH (Non-Condensing) |
| Location Rating           | Dry                | Wire Connection Type      | RJ-45                     |
| Storage Temperature       | 23° - 176° F       |                           |                           |