



Wattstopper
LMCP panel w/48-relay max capacity
Part No. LMCP48

The LMCP series panel provides simple network capable lighting control enabling the automation of lighting functions throughout an entire facility. The HDR relays in the panel can respond directly to inputs from Digital Lighting Management (DLM) switches, occupancy sensors, daylight sensors, and input modules.

Features & Benefits

Runs scheduled and photocell events autonomously	Easy setup via LMCT-100 handheld configuration tool
HDR relays include switch for manual override even when panel is powered off	Native BACnet communications for network control solutions
Compatible with Digital Lighting Management switches, sensors and input devices	99 control groups accessible via handheld configuration tool
UL 20 listed for receptacle circuit control	Compatible with DLM occupancy sensors, single pole heavy duty relays
Includes DIN-Rail for mounting NB-Router inside the panel	Optional NB-CABLES provide accessory power and data connections to NB-ROUTER (sold separately)

Specifications

General Info

Product Line	Wattstopper	Color	Nickel
UPC Number	754182934508	Country Of Origin	United States
Material	Steel	Product Series	LMCP
Installation Location	Enclosure, Wall	Application Sector	Commercial
Standard	UL 924, cUL, BAA, TAA, OSHPD Approved OSP-0257, PEP, ISO 14025:2010, ISO 14001, ISO 14040:2006, ISO 14044:2006, RoHS 2011/65/EC	Warranty Type	5-Year

Type	Relay Panel		
Dimensions			
Product Width US	23.88 in	Product Depth US	4.5 in
Product Height US	43.88 in		
Trade Programs			
BAA	Yes		
Additional Information			
Product Has Potential to Contribute to LEED	Yes	DesignLights Consortium Qualified System	Yes
Security	Yes		
Technical Information			
Operating Temperature Min	32 °F	Output Voltage	24 VDC
Timer Type	Event Based	Compatibility	LENC Enclosures
Operating Temperature Max	140 °F	Topology	Free Topology
Number of Relays	48	Input Voltage	115/277 V, 120/347 V, 240 V
Line Frequency	60 Hz	Indoor/Outdoor	Indoor
Operating Temperature	0°-60°C, 32°-140°F	Operating Humidity	5-95% RH (Non-Condensing)
Wire Connection Type	RJ-45		