



The LMDI-100 Serial Data Interface connects a Digital Lighting Management (DLM) local network to a third party system for coordinated control of devices including lighting controls, AV equipment, shade controls and user interfaces by either system.

Features & Benefits

RS-232 interface connects DLM local network to 3rd party control system	Plugs to free topology DLM local network allowing mounting in remote location
Hinged dust cover protects two RJ45 ports	Facilitates combining DLM with A/V and shade control systems
Provides access to local network data including occupancy status	Fits into standard single gang wallbox; optional DIN rail mounting

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182934362	Country Of Origin	United States
Material	ABS	Features	Electrical Isolation Rated up to 1500 V
Installation Location	Above Ceiling, Enclosure, Wall	Application Sector	Commercial
Standard	UL 2043, RS232, BAA	Warranty Type	5-Year
Type	Serial Data Device		

Dimensions

Product Width US	2.0 in	Product Depth US	2.5 in
------------------	--------	------------------	--------

Product Height US	1.6 in		
Trade Programs			
BAA	Yes		
Additional Information			
RoHS Compliant	Yes	Security	Yes
Technical Information			
Operating Temperature Min	32 °F	Compatibility	DLM Wired
Number of Connections	2	Operating Temperature Max	104 °F
Topology	Free Topology	Number of Relays	0
Indicator	Receive LED, Transmit LED	Input Voltage	24 VDC
Indoor/Outdoor	Indoor	Mounting Type	DIN Rail, Inside 2-Gang J-Box, Screw Holes
Current Draw	15 mA	Operating Temperature	0°-40°C, 32°-104°F
Operating Humidity	5-95% RH (Non-Condensing)	Location Rating	Dry
Wire Connection Type	RJ-45, Terminal Block	Storage Temperature	23° - 176° F