



Wattstopper
DLM Wired Standard Switch, 2B 2R, White
Part No. LMSW-222-W



LMSW-200 Series Wall Switches are programmable, low voltage devices for manual on/off, dimming, and scene control of one or more loads from one or more locations. They are part of the Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

Features & Benefits

Software lockable configuration button, accessible without faceplate removal

Infrared (IR) transceiver for wireless configuration and control

Each button and rocker can control individual or multiple loads. Buttons can instead control one scene. LED indicates status.

Custom engraving available to replace standard engraving

The product meets the materials restrictions of RoHS

Digital Lighting Management components plug together on a free-topology Category 5e DLM local network

Switches may be used for multi-way control

Each button can be used to dim assigned loads

Sleek single gang devices fit decorator wall plates

BAA compliant options available

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Matte	UPC Number	754182948734
Country Of Origin	China	Material	ABS
Product Series	LMSW	Switch Type	Push, Rocker
Number of Switches	4	Application Sector	Commercial
Standard	UL, cUL, FCC part 15, RoHS	Warranty Type	5-Year
Type	Switch		

Dimensions

Product Width US	1.6 in	Product Weight US	0.1 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		

Additional Information

Product Has Potential to Contribute to LEED	Yes
---	-----

Technical Information

Operating Temperature Min	0 °C	Compatibility	DLM Wired
Seismic Tested	No	Has Battery	No
Operating Temperature Max	55 °C	Number of Gangs	1
Number of Buttons	2	Number of Rockers	2
Topology	Free Topology	Input Voltage	24 VDC
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Wattage	0.168 W	Mounting Type	J-Box
Current Draw	5 mA	Operating Temperature	0°-55°C
Operating Humidity	5-95% RH (Non-Condensing)	Location Rating	Dry
Wire Connection Type	RJ-45	Engraving Type	Icon
Environmental Conditions	5 to 95%	Storage Temperature	23° - 176° F, -5° - 80° C