



Wattstopper
Discontinued - LP8 Peanut Panel w/4 Relays, 115 /277 Volts, Flush Mount
Part No. LP8F-4-115



Wattstopper's LP8 Peanut Lighting Control Panels provide simple, effective zone-based control of exterior and interior lighting in small applications. Panels control up to eight channels or zones of lighting. Zones respond to control signals from the system clock (or other signaling device) to turn lighting on and off. LP8 Panels ship pre-assembled in easy-to-install compact packages available for surface and flush mounting. They consist of relays, a system clock, panel intelligence, power supply, tub and cover. The standard enclosure is NEMA 1-rated.

Features & Benefits

Simple and effective interior and exterior lighting control

Controls up to eight single-pole lighting circuits

Easy user interface with on-screen help

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	LC8-120/277
Color	Black	Finish	Painted
UPC Number	754182922970	Country Of Origin	United States
Material	Steel	Product Series	LP8
Features	8 Inputs for Low Voltage Switches, LCD Screen	Installation Location	Wall
Application Sector	Commercial	Standard	UL 20, UL, BAA
Warranty Type	1-Year	Type	Relay Panel

Dimensions

Product Width US	16.5 in	Product Depth US	4.6 in
Product Height US	15.1 in		

Trade Programs

BAA Yes

Additional Information

RoHS Compliant Yes DesignLights Consortium Qualified System Yes

Security Yes

Technical Information

Operating Temperature Min 32 °F Output Voltage 24 VDC

Timer Type Astronomical Load Rating 20 A @ 120/347 VAC, 30 A @ 277 VAC

Compatibility AS-100, EM-24D2, LVSW Horsepower Rating 1-1/2 HP @ 120 VAC

Bus Power Supply 800 mA @ 24 VDC Operating Temperature Max 139 °F

Enclosure Type NEMA 1 Number of Poles Single Pole

Number of Relays 4 Indicator Relay Status LED

Input Voltage 115/277 VAC Line Frequency 50 Hz, 60 Hz

Indoor/Outdoor Indoor Mounting Type Flush, Screw Holes

Operating Temperature 32°-139°F Operating Humidity 5-95% RH (Non-Condensing)

Location Rating Dry Storage Temperature 23° - 176° F