



Wattstopper
Low Voltage Wall Switch, 1-Button w/LED, White
Part No. LVSW-101-W



LVSW-100 Series Low Voltage Switches are lighting control devices that use conventional point-to-point low voltage wiring for control of single or multiple loads. Each button provides a momentary contact that is intended for use with compatible low voltage relay panels or similar lighting control panels or devices. Each button has an LED indicator that can serve as a status indicator or as a locator light.

Features & Benefits

Sleek single gang devices fit decorator wall plates (not supplied); 1-, 2-, 3-, 4-, and 8-button models

Blue LED indicator on each button can be used as a locator light or as a status indicator

Five color options and custom engraving options; standard buttons may be replaced in the field

The product meets the materials restrictions of RoHS

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Gloss	UPC Number	754182931309
Country Of Origin	China	Material	ABS
Product Series	LVSW	Switch Type	Push
Number of Switches	1	Application Sector	Commercial
Standard	UL, cUL, RoHS	Warranty Type	5-Year
Type	Switch		

Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		

Additional Information

RoHS Compliant Yes

Technical Information

Operating Temperature Min	0 °C	Compatibility	LC8, LP8
Seismic Tested	No	Has Battery	No
Operating Temperature Max	55 °C	Number of Gangs	1
Number of Buttons	1	Number of Rockers	0
Input Voltage	24 VDC	Indoor/Outdoor	Indoor
Mounting Type	J-Box	Current Draw	2 mA
Operating Temperature	0°-55°C	Operating Humidity	5-95% RH (Non-Condensing)
Location Rating	Dry	Wire Connection Type	Screw Terminal
Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C