



Wattstopper 16 port Ethernet switch for LSM, DIN mounting Part No. NB-SWITCH-16



The NB-SWITCHES are enterprise-grade Ethernet switches that work with up to four or seven NB-ROUTERS to provide high speed connectivity for Digital Lighting Management (DLM) networked systems. The compact switch has a rugged metal enclosure and integral DIN rail clip.

Features & Benefits

100 Mbps 5-port, 8-port and 16-port Ethernet switches 10BASE-T/100BASE-TX/ 100BASE-T operation

Auto negotiation of speed and duplex Compatible with DLM Segment Manager or third party BACnet building automation systems

Specifications

General Info

Product Line	Wattstopper	Color	Gray
Finish	Painted	UPC Number	754182931286
Country Of Origin	United States	Material	Steel
Product Series	NB	Features	Unmanaged Switch
Installation Location	Enclosure, Wall	Application Sector	Commercial
Standard	IP30, RoHS, UL 508, BAA	Warranty Type	1-Year
Type	Network Switch		

Dimensions

Product Width US	3.79 in	Product Weight US	2.0 lb
Product Height US	1.61 in	Product Length US	6.02 in

Trade Programs

BAA	Yes
-----	-----

Additional Information

RoHS Compliant	Yes	DesignLights Consortium Qualified System	Yes
Security	Yes		

Technical Information

Operating Temperature Min	32 °F	Compatibility	DLM Wired
Number of Connections	16	Power Supply	10-36 VDC, 24 VAC
Operating Temperature Max	140 °F	Data Transfer Rate	100 Mbps
Indicator	Network Status LED, Power LED	Connector Type	RJ-45
Input Voltage	24 VDC/VAC	Indoor/Outdoor	Indoor
Mounting Type	DIN Rail	Operating Temperature	0°-60°C, 32°-140°F
Operating Humidity	10-95% RH (Non-Condensing)	Storage Temperature	-40° - 85° C