



Wattstopper Discontinued - Digital Switch, 2-button w/infrared, White, USA Part No. LMSW-102-W-U



LMSW-100 Series Wall Switches are low voltage devices for energy-saving manual on/off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

Features & Benefits

Low voltage pushbutton switches for control of multiple loads	Components of Digital Lighting Management integrated control system
Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors	Customizable buttons with LED status indicators
IR transceiver for wireless configuration and remote control	Plug n' Go automatic configuration and Push n' Learn for personalization

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Gloss	UPC Number	754182927692
Country Of Origin	United States	Material	ABS
Product Series	LMSW	Switch Type	Push
Number of Switches	2	Application Sector	Commercial
Standard	UL, cUL, FCC part 15, RoHS, BAA, TAA	Warranty Type	5-Year
Type	Switch		

Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		

Additional Information

RoHS Compliant	Yes	Security	Yes
----------------	-----	----------	-----

Technical Information

Operating Temperature Min	0 °C	Compatibility	DLM Wired
Has Battery	No	Operating Temperature Max	55 °C
Number of Buttons	2	Number of Rockers	0
Topology	Free Topology	Input Voltage	24 VDC
Indoor/Outdoor	Indoor	Mounting Type	J-Box
Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Location Rating	Dry
Wire Connection Type	RJ-45	Engraving Type	Blank
Storage Temperature	23° - 176° F, -5° - 80° C		