



Wiremold
24S6012GBA99IV Steel Plugmold® Multioutlet Strip
Part No. 24S6012GBA99IV



5' Steel Plugmold Multioutlet Strip with 5 duplex receptacles spaced at 12" GBA

Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation with greater wire capacity than V2000.

Ivory ScuffCoat finish. Durable scratch resistant finish.

Removable cover. Allows easy access to wiring for changes or additions.

Full range of fittings. Provides a complete wiring solution.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 20A, 120V receptacles. Ideal for short runs requiring additional outlets in electrically busy areas.

Single or alternating circuit. Meets virtually any circuit requirement.

Choice of receptacle spacing. Center spacing between receptacles of 6", 12" and 18".

Simplex receptacle. More spacing options available.

Duplex receptacle. Aesthetically pleasing, functional 20A duplex for the 24S (2400) Series.

Customization available. All products can be modified to accommodate virtually any application.

Specifications

General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776165173	Country Of Origin	United States
Material	Steel	Product Series	2400 Series

Number of Receptacles	5	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail
Standard	cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover& Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Plugmold	Installed Devices	Duplex Receptacle
Dimensions			
Product Width US	1.9062 in	Product Weight US	4.9 lb
Product Depth US	0.9 in	Product Height US	0.875 in
Product Length US	60.0 in	Receptacle Spacing	12 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Is Pre-Wired	Yes	Wiring Configuration	Dual Circuit
Amperage	20 A	Indoor/Outdoor	Indoor
Wiring Method	Hard-Wired	NEMA Configuration Code	5-20R
Mounting Type	On Surface	Voltage	125.0 V
Environmental Conditions	Dry interior locations		