




Wiremold
Ratchet-Pro 881 Series Multiple Service Floor Box Cover Kit
Part No. 881RC4ATCBS



For 881PVC Floor Box. Kit complete with two (2) 20A duplex receptacles, (receptacles can be wired as standard or Isolated Ground), flange and slide holder, 881ADP Adapter, and 881DIV Divider. Provided with Wiremold CM Series Open System unloaded adapters, Ortronics Series II and TracJack adapters. Modular jacks sold separately. CAUTION: Not for use on concrete pours less than 4 1/2" (114mm) deep. Not for use when concrete is the finished floor. Use only for tile, carpet, or wood covered floors.

Features & Benefits

For 881PVC Floor Box. Kit complete with two (2) 20A duplex receptacles, Provided with Wiremold CM Series Open System (receptacles can be wired as standard or Isolated Ground), flange and unloaded adapters, Ortronics Series II and TracJack adapters. Modular jacks sold separately.

CAUTION: Not for use on concrete pours less than 4 1/2" (114mm) deep. Not for use when concrete is the finished floor. Use only for tile, carpet, or wood covered floors.

Specifications

General Info

Product Line	Wiremold	Finish	Brushed
UPC Number	786564013129	Country Of Origin	Mexico
Material	Stainless Steel	Construction	Not Assembled
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	cULus Listed Nonmetallic Outlet Boxes: File E110748 Guide QCMZ. Meets Article 314.27(C) of NEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Cover

Dimensions

Product Width US	8.25 in	Product Weight US	4.51 lb
------------------	---------	-------------------	---------

Product Depth US	8.25 in
------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E110748	cULus Listed	Yes
---------------------	---------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Service Capacity	Multiple	Cable Entry	Through Floor
------------------	----------	-------------	---------------

Number of Outlets	4
-------------------	---