



Wiremold
20GB512 Steel Plugmold® Multioutlet System
Part No. BK20GB512



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

This product meets the material restrictions of RoHS.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776074536	Country Of Origin	United States
Material	Steel	Product Series	2000 Series

Number of Receptacles		5	Application Sector		Commercial, Education, Entertainment, Healthcare, Hospitality, Retail
Standard		cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover& Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.			1-Year from Installation or 2-Years from Day of Sale
Type		Plugmold	Installed Devices		Single Receptacle
Dimensions					
Product Width US		1.3 in	Product Weight US		2.93 lb
Product Depth US		0.75 in	Product Height US		0.75 in
Product Length US		60.0 in	Receptacle Spacing		12 in
Listing Agencies / 3rd Party Agencies					
cULus ListingNumber		E15191	cULus Listed		Yes
Additional Information					
RoHS Compliant		Yes	Product Environmental Profile		Yes
Technical Information					
Is Pre-Wired		Yes	Wiring Configuration		Single Circuit
Amperage		15 A	Indoor/Outdoor		Indoor
Wiring Method		Hard-Wired	NEMA Configuration Code		5-15R
Mounting Type		On Surface	Voltage		125.0 V

Environmental Conditions Dry interior locations
