



Wiremold
ModPower Middle Unit, In Surface
Part No. MDCF3-MG



People move. Equipment moves. Furniture moves. Power must be easy to change and relocate. The industry's first code compliant modular power system is designed to give you the freedom to reconfigure power and charging as you need. No matter how your project unfolds, the ModPower System provides convenient power access that meets code.

Features & Benefits

Modular code-compliant power listed for use in US and Canada. Connect up to six of our power units together to create a system of power for training spaces, workstations or flexible spaces.

On surface units can be mounted using clamp (for a damage-free install) or can be installed using wood screws. Installation for in surface units is a snap: Simply cut the opening, insert the unit, tighten the clamps, snap on the bezel and plug it in.

FCC Compliance. This device complies with part 15 of the FCC Rules.

Tamper resistant receptacles. Models have three tamper resistant receptacles to keep little fingers away from danger.

Choose in surface or on surface. Pick the option that best fits your space: in surface or on surface. On surface units can be mounted under or above table surfaces. In surface units include a bezel that hides the mounting screws for a cleaner look.

UL Spill Water Compliant. Passed UL 962A spill water test requirements so it can be used in a horizontal surface, such as a tabletop.

You will notice that our units (primary, middle and end) all utilize a circuit breaker. UL962A Supplement SD requires that all furniture power distribution units for portable (moveable) workspace tables contain supplementary overcurrent protection.

Maximum number of interconnected units in a system vary depending on region. Maximum of 6 units in a system allowed in USA. Maximum of 4 units in a system allowed in Canada.

Specifications

General Info

Product Line	Wiremold	Color	Magnesium
UPC Number	786776195156	Country Of Origin	China
Material	Plastic	Number of Receptacles	3
Features	USB-A Charging, USB-C Charging	Outlet Type	Tamper-Resistant

Application Sector	Commercial, Education, Hospitality	Standard	UL Listed to UL962A Supplement SD – Furniture Power Distribution Units for Portable (Moveable) Work Space Tables: File E349493 Guide IYNC, CSA certified to CSA Standard C22.2 No. 203-16 Modular Wiring Systems for Office Furniture
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Modular Power System
Dimensions			
Product Width US	2.75 in	Product Weight US	2.438 lb
Product Height US	2.625 in	Product Length US	7.625 in
Internal Depth	2.625 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	CSA File Number	161600 (LR 350)
FCC Compliant	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
USB Wattage	15 W	USB Amperage	3.1 A
Cord Length	3 ft	Number of USBs	2
Amperage	12 A	Wiring Method	Cord-ended
NEMA Configuration Code	5-15R	Mounting Type	In Surface
Cutout Shape	Rectangular	Voltage	125.0 V