



Wattstopper
Low Voltage Switch, 4-Button w/LED, Black
Part No. LVSW-104-B



LVSW-100 Series Low Voltage Switches are lighting control devices that use conventional point-to-point low voltage wiring for control of single or multiple loads. Each button provides a momentary contact that is intended for use with compatible low voltage relay panels or similar lighting control panels or devices. Each button has an LED indicator that can serve as a status indicator or as a locator light.

Features & Benefits

Low voltage pushbutton switches for on/off control of one or more loads

Compatible with LC8, LP8, LI and LMCP Series lighting control panels

LED pilot light on each button

Customizable, field replaceable buttons

Single gang devices, compatible with standard decorator style face plates

Appearance matches DLM LMSW-100 Series digital wall switches

Specifications

General Info

Product Line	Wattstopper	Color	Black
Finish	Gloss	UPC Number	754182931491
Country Of Origin	China	Material	ABS
Product Series	LVSW	Switch Type	Push
Number of Switches	4	Application Sector	Commercial
Standard	UL, cUL, RoHS	Warranty Type	5-Year
Type	Switch		

Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		

Additional Information

RoHS Compliant Yes

Technical Information

Operating Temperature Min 0 °C Compatibility LC8, LP8

Seismic Tested No Has Battery No

Operating Temperature Max 55 °C Number of Gangs 1

Number of Buttons 4 Number of Rockers 0

Input Voltage 24 VDC Indoor/Outdoor Indoor

Mounting Type J-Box Current Draw 2 mA

Operating Temperature 0°-55°C Operating Humidity 5-95% RH (Non-Condensing)

Location Rating Dry Wire Connection Type Screw Terminal

Engraving Type Blank Storage Temperature 23° - 176° F, -5° - 80° C