



Wiremold
Charging Station, 3-Gang, Unwired - Black
Part No. XCSPP3G-BK



The Power Pedestal is ideal for areas that are already illuminated, such as outdoor dining areas. Shorter height enables use besides tables or as a lower-profile solution in landscaping. 3-gangs, unwired.

Features & Benefits

Combine power with area lighting in one pedestal to maximize functionality of outdoor spaces.

Durable, Premium Finishes – Available in three outdoor-rated finishes to complement your space design. Choose from black, bronze or silver.

Add up to two pairs of shelves to hold mobile devices while charging

Enables pedestal to support outdoor presentation areas and classrooms, eliminating the need to bring cables from inside a building.

Outdoor-Rated Construction – Rugged aluminum form designed for durability in all weather conditions. UL listed to NEMA 3R requirements to ensure optimal performance.

Add an A/V-Communication Kit to 3-gang versions to accommodate Wiremold AVIP plates as well as decorator A/V or communication devices.

Interior illuminates when door is open. Replace standard color-matched door with a transparent version to make devices inside more visible. Or, select a lockable door for added security or to ensure use is limited to facility personnel.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776186413	Country Of Origin	Mexico
Material	Aluminum	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit

Standard	cULus Listed, File Number E479489, Guide PUPR	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Charging Stations		
Dimensions			
Product Width US	6.0 in	Product Height US	34.0 in
Product Length US	8.0 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E479489	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Operating Temperature Min	-31 °F	Is Pre-Wired	No
Service Capacity	Single	Operating Temperature Max	140 °F
Number of Gangs	3	Enclosure Type	NEMA 3R
Number of Channels	1	Lighting Types	No Light
Operating Temperature	-31°F-140°F	Maximum Amperage Supported	20 A