



Wiremold
800CILCK Series Cast-Iron Floor Box
Part No. 800CILCK



This semi-adjustable cast iron floor box provides an excellent and economical activation solution for the low density power or communication requirements for on-grade open space areas. These boxes feature an aesthetic, low profile brass appearance that allows you to activate your wiring without obstructions. Activations for these boxes can be flush or pedestal type. These boxes also accept the 525 Series Service Fittings, allowing for more configuration options and a die-cast aluminum look. Typical applications would be in any large open space area.

Features & Benefits

Stamped steel construction. Meets requirements for above grade applications. Lower cost alternative to cast iron boxes on above grade applications.

Activation flush or pedestal. Flexibility to meet power or data wiring requirements. Variety of aesthetically pleasing cover options.

Single power receptacles available. An inexpensive option for low density power requirements for open space areas.

Covers are interchangeable for cast iron and stamped steel. More activations to meet any decor.

Specifications

General Info

Product Line	Wiremold	UPC Number	786564262367
Country Of Origin	United States	Material	Cast Iron
Construction	Assembled	Cover Style	Flush
Cover Material	Brass	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

Dimensions

Product Weight US	4.27 lb	Product Height US	3.375 in
-------------------	---------	-------------------	----------

Product Length US	4.187 in	Cubic Capacity	28.3 in³
Knockout Size	1/2 in, 3/4 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Floor Type	Carpet, Concrete, Tile	Service Capacity	Single
Box Capacity	1 Gang	Cable Entry	Knockout
Box Type	On-Grade	Depth Behind Device Plates	2.6 in