




Wiremold  
RFB9 and RFB11 Series GFI Receptacle Device Plate  
Part No. RFB119-GFI



One-gang device plate in standard (GFI) widths.

## Features & Benefits

One-gang device plate in standard (GFI) widths.

## Specifications

### General Info

|                    |                                                      |              |                                                                                           |
|--------------------|------------------------------------------------------|--------------|-------------------------------------------------------------------------------------------|
| Product Line       | Wiremold                                             | UPC Number   | 786776030143                                                                              |
| Country Of Origin  | Mexico                                               | Construction | Unassembled                                                                               |
| Application Sector | Commercial                                           | Standard     | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC. |
| Warranty Type      | 1-Year from Installation or 2-Years from Day of Sale | Type         | Device Plate                                                                              |

### Dimensions

|                   |         |                   |          |
|-------------------|---------|-------------------|----------|
| Product Width US  | 2.75 in | Product Weight US | 0.095 lb |
| Product Height US | 4.5 in  |                   |          |

### Listing Agencies / 3rd Party Agencies

|                     |       |              |     |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

---

Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---