



Wiremold
20GB206 Steel Plugmold® Multioutlet system
Part No. S20GB206



2' Plugmold Multioutlet System with 6 single outlets

Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

Specifications

General Info

Product Line	Wiremold	Color	Stainless Steel
UPC Number	786776084856	Country Of Origin	United States
Material	Stainless Steel	Product Series	2000 Series

Number of Receptacles		4	Application Sector		Commercial, Education, Entertainment, Healthcare, Hospitality, Retail
Standard		cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover& Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.			1-Year from Installation or 2-Years from Day of Sale
Type		Plugmold	Installed Devices		Single Receptacle
Dimensions					
Product Width US		1.3 in	Product Weight US		1.29 lb
Product Depth US		0.75 in	Product Height US		0.75 in
Product Length US		24.0 in	Receptacle Spacing		6 in
Listing Agencies / 3rd Party Agencies					
cULus ListingNumber		E15191	cULus Listed		Yes
Additional Information					
RoHS Compliant		Yes	Product Environmental Profile		Yes
Technical Information					
Is Pre-Wired		Yes	Wiring Configuration		Single Circuit
Amperage		15 A	Indoor/Outdoor		Indoor
Wiring Method		Hard-Wired	NEMA Configuration Code		5-15R
Mounting Type		On Surface	Voltage		125.0 V

Environmental Conditions Dry interior locations
