



Wiremold
20GB512 Steel Plugmold® Multioutlet System
Part No. S20GB512



5' Plugmold Multioutlet System with 5 single outlets, GB

Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

This product meets the material restrictions of RoHS.

Specifications

General Info

Product Line	Wiremold	Color	Stainless Steel
UPC Number	786776084894	Country Of Origin	United States
Material	Stainless Steel	Product Series	2000 Series

Number of Receptacles		5	Application Sector		Commercial, Education, Entertainment, Healthcare, Hospitality, Retail	
Standard		cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover& Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.		Warranty Type		1-Year from Installation or 2-Years from Day of Sale
Type		Plugmold		Installed Devices		Single Receptacle
Dimensions						
Product Width US		1.3 in		Product Weight US		3.03 lb
Product Depth US		0.75 in		Product Height US		0.75 in
Product Length US		60.0 in		Receptacle Spacing		12 in
Listing Agencies / 3rd Party Agencies						
cULus ListingNumber		E15191		cULus Listed		Yes
Trade Programs						
USMCA		Yes				
Additional Information						
RoHS Compliant		Yes		Product Environmental Profile		Yes
Technical Information						
Is Pre-Wired		Yes		Wiring Configuration		Single Circuit

Amperage	15 A	Indoor/Outdoor	Indoor
Wiring Method	Hard-Wired	NEMA Configuration Code	5-15R
Mounting Type	On Surface	Voltage	125.0 V
Environmental Conditions	Dry interior locations		